



KOCH CHEMIE · KOCH-CHEMIE · COMPOUNDS & POLISHES

ONE CUT & FINISH P6.02

HIGH GLOSS POLISH WITH SEALANT

SKU

469250US

250ML

1L

469001US

The One Cut & Finish P6.02 is a machine polish for the permanent removal of polishing haze, holograms and scratches as well as sanding from grit P 2000 with a simultaneous sealing effect. A brilliant and durable high-gloss finish is created through the use of homogeneous abrasives.

PERFORMANCE

ROLE	Polish
SURFACES / AREAS	Paints on cars, commercial vehicles, motorcycles, etc.
ABRASION / CUT	6.0 (PI)
GLOSS LEVEL	8.0 (PI)
PH	8.2 (SDS)
APPEARANCE	Orange · Characteristic (SDS)
DENSITY	1.06 g/cm ³ (SDS)
SOLUBILITY	Mixable (SDS)

APPLICATION & PHYSICAL

METHOD	To achieve optimal results, we recommend processing with our One Cut Pad and a high-performance eccentric (min).
VOC	< 0,1 % (SDS)
TRANSPORT	Not regulated for transport (SDS §14)
WARNINGS (PI)	Shake before use. Check for suitability and compatibility before use. Do not apply to hot surfaces. Protect from frost and excessive heat. Do not use on painted plastics and rubber
MDSC SIZES	250ml (469250US), 1L (469001US)

OVERVIEW

The One Cut & Finish P6.02 is a machine polish for the permanent removal of polishing haze, holograms and scratches as well as sanding from grit P 2000 with a simultaneous sealing effect. A brilliant and durable high-gloss finish is created through the use of homogeneous abrasives. The innovative One Cut & Finish P6.02 combines an optimal ratio of abrasiveness and gloss for economical and effective work in vehicle preparation. The One Cut & Finish P6.02 is economical, easy to polish and easy to wipe off. Contains carnauba wax and non-volatile silicones. SDS signal word: Warning.

DIRECTIONS

- 1 To achieve optimal results, we recommend processing with our One Cut Pad and a high-performance eccentric (min.
- 2 15 mm stroke) or with an eccentric with forced rotation.
- 3 For optimal dosing, spread five pea-sized drops evenly on the pad.
- 4 Distribute the polish evenly over the surface with the machine at the lowest speed and then polish crosswise with medium pressure.
- 5 Do not alternate the sponges used for this product with other products. For the scratch-free removal of polish residues, we recommend our ultrasonically cut Polish & Sealing Towel.
- 6 PI warnings: Shake before use. Check for suitability and compatibility before use. Do not apply to hot surfaces. Protect from frost and excessive heat. Do not use on painted plastics and rubber

SAFETY SNAPSHOT

WARNING

Skin Sens. 1 · H317-May cause an allergic skin reaction. · EUH066ess or cracking. · EUEUH066ess or cracking.

APPEARANCE	Orange · Characteristic
PH / DENS.	8.2 · 1.06 g/cm ³
TRANSPORT	Not regulated for transport (SDS §14)
VOC	< 0,1 %

Manufacturer SDS — Koch-Chemie One Cut & Finish P6.02 —

SOURCES

1. Manufacturer Product Information (Koch-Chemie) — https://www.koch-chemie.com/pdf/datasheet/One_Cut_Finish_P602_en.pdf
2. Manufacturer SDS (Koch-Chemie One Cut & Finish P6.02) — https://media.koch-chemie.com/pdf/SDBL/One_Cut_&_Finish_P6-02_Art-___469999_469999_0005_EN.pdf
3. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailssupply.com/products/koch-chemie-one-cut-finish>