



MENZERNA · COMPOUNDS & POLISHES

MENZERNA 3IN1 CUT, GLOSS, AND WAX

ONE-STEP MEDIUM CUT · FINISH · WAX SEAL

SKU

M-3IN1Q

1 LITER

All-in-one medium-cut polish that removes P3000 sanding marks, finishes to high gloss, and adds wax protection in a single product; silicone-free and overpaintable (mfr product page / EN TDS OSP 3in1).

PERFORMANCE

ROLE	Medium cut + finish + wax protection one-step polish (mfr product page / EN TDS)
CUT / GLOSS (MFR)	Cut 5 · Gloss 9 (mfr product page / EN TDS)
MAX ABRASION (TDS)	P3000 (EN TDS / product page)
SERVICE LIFE (MFR)	1 month (mfr product page)
SILICONE-FREE	Yes — silicone-free; can be overpainted (mfr product page / EN TDS)

APPLICATION & PHYSICAL

PADS (MFR)	Medium Cut Foam Pad; optional Soft Cut / Wax Foam Pad; hand applicator published (mfr product page / EN TDS)
ROTARY SPEED (TDS)	Start 1,250–1,500 rpm · End 500–800 rpm (EN TDS / product page)
ORBITAL (TDS)	Start medium speed · End lower speed range (EN TDS / product page)
PRESSURE (TDS)	Start medium · End low (EN TDS)
STORAGE (TDS)	5–30 °C; avoid frost and direct sunlight (EN TDS)
DENSITY (TDS)	1.0 kg/l · Viscosity 9–15 Pas (EN TDS)
PACK SIZES (CATALOG)	1 liter

OVERVIEW

All-in-one medium-cut polish that removes P3000 sanding marks, finishes to high gloss, and adds wax protection in a single product; silicone-free and overpaintable (mfr product page / EN TDS OSP 3in1).

DIRECTIONS

- 1 Clean the surface thoroughly prior to polishing (mfr product page / EN TDS).
- 2 Shake the bottle and apply to Medium Cut Foam Pad — 3–4 / 5 / 6–7 pea-sized drops for Ø95 / 150 / 180 mm pads on a ~40×40 cm area (EN TDS).
- 3 Rotary or orbital with cross-coating, or hand applicator (mfr product page / EN TDS).
- 4 Begin with moderately strong pressure at medium machine speed; reduce pressure and speed in final cycles (mfr product page / EN TDS).
- 5 Work until only a slightly transparent/oily film remains (mfr product page / EN TDS).
- 6 Leave to dry 5–10 minutes, then wipe with Premium microfiber without pressure (mfr product page / EN TDS).
- 7 Optional reapply with Wax Foam Pad for an even better finish (mfr product page / EN TDS).

SAFETY SNAPSHOT

NOT CLASSIFIED UNDER GHS (MFR SDS §2)

GHS label elements / signal word / hazard statements: Void — product not classified according to GHS on SDS (mfr SDS §2). Keep out of reach of children.

PHYSICAL STATE Viscous · Whitish / creamy · Characteristic odor (SDS §9 / EN TDS colour Creamy)

PH (20 °C) >7 (SDS §9)

FLASH POINT >100 °C / >212 °F (SDS §9)

DENSITY (20 °C) 1 g/cm³ (SDS §9); 1.0 kg/l (EN TDS)

VOC 147.3 g/l (SDS §9; % not printed as a standalone line on this SDS)

WATER SOLUBILITY Not miscible or difficult to mix (SDS §9)

Manufacturer SDS — One-Step Polish 3in1 →

SOURCES

1. Manufacturer tech data / product information — https://www.menzerna.com/fileadmin/ns_theme_menzerna/Dokumente/Technische_Datenblaetter/Autopolituren/EN/TDB_10_One_Step_Polish_3in1_EN_09.2021.pdf
2. Manufacturer product page — <https://www.menzerna.com/car-care/car-polish/products/details/one-step-polish-3in1>
3. Manufacturer SDS (One-Step Polish 3in1) — <https://menzernausa.com/wp-content/uploads/2016/04/3in1.pdf>
4. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailssupply.com/products/menzerna-3in1-cut-gloss-and-wax>
5. Mapping note — Catalog '3in1 Cut, Gloss, and Wax' maps to manufacturer One-Step Polish 3in1 / OSP 3in1 (article 22748). Product page publishes service life 1 month.
6. Omissions — Dilution ratio not published (ready-to-use polish); VOC % not printed as a standalone percentage on this SDS (g/l published)