



AUTOFIBER · AUTOFIBER.COM · APPLICATORS

MICROFIBER FINGERTIP MITT APPLICATOR

FINGER APPLICATOR · 5" × 4"

SKU

MIT305BLHALF

Finger-mitt applicator for dressings, trim restore, wax/sealant (mfr).

PERFORMANCE

TYPE	Microfiber fingertip mitt applicator (mfr)
SIZE	5" × 4" (mfr)
COVERAGE	Covers 3–4 fingers depending on hand size (mfr)

APPLICATION & PHYSICAL

MDSC SKU	MIT305BLHALF
USE	Dressings, trim restoration, wax/sealant; wheels & interior crevices (mfr)
MFR LISTING	Sold as 6-pack on Autofiber (MIT305BLHALF-6)

OVERVIEW

Autofiber Finger Applicator microfiber mitt (5×4) covers several fingers for controlled application of dressings, trim restorers, wax, and sealants in tight spaces (mfr).

DIRECTIONS

- 1 Slide mitt over fingertips; load product sparingly.
- 2 Apply to trim, wheels, or interior crevices as needed.
- 3 Wash or replace when loaded.

SAFETY SNAPSHOT

**ARTICLE — NOT A CHEMICAL
PRODUCT; NO SDS TYPICALLY
PUBLISHED**

Textile / tool article. Follow Autofiber care guidance; wash microfiber separately without fabric softener.

SIZE	5" × 4"
FORM	Finger mitt

Manufacturer SDS not retrieved for this article (towels/tools are articles — SDS often N/A) or see Autofiber downloads / local archive.

SOURCES

1. Manufacturer source — <https://www.autofiber.com/products/finger-applicator-microfiber-fingertip-mitt-applicator-5-in-x-4-in-6-pack>
2. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailsupply.com/products/microfiber-fingertip-mitt-applicator>
3. Mapping note — MDSC SKU without pack suffix; Autofiber lists MIT305BLHALF-6 (6 pack) product page.
4. Omissions — MDSC SKU lacks pack suffix; mfr page is 6-pack listing.
5. Document type — product_page