



AUTOFIBER · AUTOFIBER.COM · APPLICATORS

THIN SAVER APPLICATOR — HALF TERRY / HALF SUEDE

SAVER APPLICATOR · THIN · HALF/HALF · ONE SIDE SUEDE / ONE TERRY

SKU

SSTX301GYB

Thin dual-face Saver Applicator (mfr SSTX101).

PERFORMANCE

TYPE	Thin half/half Saver Applicator (mfr)
FACES	One side suede, one side terry (mfr)
BARRIER	Hydrophobic barrier (mfr)
MFR SKU MAP	SSTX101GYB-12

OVERVIEW

Autofiber Saver Applicator adds a hydrophobic barrier between microfiber and sponge so low-viscosity coatings waste less product into the foam core (mfr). Thin half/half mapped MDSC SSTX301GYB → Autofiber SSTX101GYB-12 (mfr).

DIRECTIONS

- 1 Apply coating/sealant sparingly to the microfiber face (barrier limits soak-through).
- 2 Spread in even overlapping passes; do not flood the sponge core.
- 3 Replace applicator when face loads or coating begins to tack on the pad.

APPLICATION & PHYSICAL

MDSC SKU	SSTX301GYB
USE	Coatings — choose face per product (mfr)

SAFETY SNAPSHOT

ARTICLE — NOT A CHEMICAL PRODUCT; NO SDS TYPICALLY PUBLISHED

Textile / tool article. Follow Autofiber care guidance; wash microfiber separately without fabric softener.

FACES Terry + Suede

THICKNESS CLASS Thin

Manufacturer SDS not retrieved for this article (towels/tools are articles — SDS often N/A) or see Autofiber downloads / local archive.

SOURCES

1. Manufacturer source — <https://www.autofiber.com/products/thin-saver-applicator-half-half-microfiber-coating-applicator-sponge-with-plastic-barrier-one-side-suede-one-side-terry-12-pack>
2. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailssupply.com/products/autofiber-thin-saver-applicator-half-half-microfiber-coating-applicator-sponge-with-plastic-barrier-one-side-suede-one-side-terry>
3. Mapping note — MDSC SKU SSTX301GYB Thin Half/Half; Autofiber thin half/half is SSTX101GYB-12.
4. Omissions — MDSC SSTX301GYB vs mfr SSTX101GYB-12.
5. Document type — product_page