



AUTOFIBER · AUTOFIBER.COM · APPLICATORS

THICK SAVER APPLICATOR — SUEDE

SAVER APPLICATOR · THICK · SUEDE · ~5" × 3" × 1.75"

SKU

SSX201GYB

Thick suede Saver Applicator with plastic barrier (mfr).

PERFORMANCE

TYPE	Thick suede Saver Applicator (mfr)
SIZE	~5" × 3" × 1.75" (mfr)
FACE	Suede microfiber (mfr)
BARRIER	Hydrophobic barrier (mfr)

OVERVIEW

Autofiber Saver Applicator adds a hydrophobic barrier between microfiber and sponge so low-viscosity coatings waste less product into the foam core (mfr). Thick suede variant (mfr SSX201GYB-12).

DIRECTIONS

1. Apply coating/sealant sparingly to the microfiber face (barrier limits soak-through).
2. Spread in even overlapping passes; do not flood the sponge core.
3. Replace applicator when face loads or coating begins to tack on the pad.

APPLICATION & PHYSICAL

MDSC SKU	SSX201GYB
USE	Coatings — suede face feel (mfr)

SAFETY SNAPSHOT

**ARTICLE — NOT A CHEMICAL
PRODUCT; NO SDS TYPICALLY
PUBLISHED**

Textile / tool article. Follow Autofiber care guidance; wash microfiber separately without fabric softener.

FACE Suede
THICKNESS CLASS Thick

Manufacturer SDS not retrieved for this article (towels/tools are articles — SDS often N/A) or see Autofiber downloads / local archive.

SOURCES

1. Manufacturer source — <https://www.autofiber.com/products/saver-applicator-smooth-microfiber-suede-applicator-sponge-with-plastic-barrier-blue-gray-12-pack>
2. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailsupply.com/products/thick-autofiber-microfiber-suede-applicator-sponge-with-plastic-barrier>
3. Omissions — MDSC SKU without -12; mfr SSX201GYB-12.
4. Document type — product_page