



XANIGO MARINE · MAINTENANCE

XANIGO MARINE WATERLESS WASH (QUART)

WATERLESS CLEANER · MOLD-SYSTEM NEUTRALIZER

SKU

XMAP32

32 OZ.

Hose-free waterless wash used between Mold & Mildew Preventer applications and to neutralize Mold & Mildew Stain Remover residue so preventer can bond. Manufacturer positions it for seats, life jackets, vinyl, canvas, ropes, carpet, and other high-moisture areas without harsh chemicals or running water.

PERFORMANCE

ROLE	Waterless wash / neutralizer in mold & mildew prevention system (product page)
HOSE REQUIRED	No — no hose or running water needed (product page)
SYSTEM STEP	Apply after rinsing Mold & Mildew Stain Remover to neutralize harsh chemicals before Preventer (product page / protocol QG)
SURFACES (MFR)	Seats, life jackets, vinyl, canvas, ropes, carpet, high-moisture areas (product page)
CHEMISTRY NOTE (CASE PAGE)	Patented organosilane compound · water based · no alcohol · non-flammable (case product page)
SHELF LIFE (CASE PAGE)	1.5 years unopened · 1 year opened (case product page)

APPLICATION & PHYSICAL

METHOD	Spray onto surface and wipe with microfiber to clean / neutralize (protocol QG / product page)
PACK SIZE (CATALOG)	32 oz.

OVERVIEW

Hose-free waterless wash used between Mold & Mildew Preventer applications and to neutralize Mold & Mildew Stain Remover residue so preventer can bond. Manufacturer positions it for seats, life jackets, vinyl, canvas, ropes, carpet, and other high-moisture areas without harsh chemicals or running water.

DIRECTIONS

- 1 Use after rinsing Mold & Mildew Stain Remover: spray Waterless Wash onto the surface and wipe in with a microfiber cloth to neutralize residual remover (manufacturer protocol quick guide).
- 2 Between Preventer applications, use Waterless Wash to clean seats and remove sunscreen without impacting the protective layer (manufacturer protocol quick guide).
- 3 No hose or running water required (manufacturer product page).

SAFETY SNAPSHOT

Manufacturer SDS published on [xanigomarine.com](https://www.xanigomarine.com/sds) SDS page (scanned PDF — limited text extract). Follow product label and SDS.

[Manufacturer SDS — Waterless Wash & Neutralizer —](#)

SOURCES

1. Manufacturer tech data / product information — <https://www.xanigomarine.com/products/xanigo-marine-waterless-wash-quart>
2. Manufacturer Instruction & Guarantee Handbook — <https://productimageserver.com/literature/quickGuide/104290QG.pdf>
3. Manufacturer SDS (Waterless Wash & Neutralizer) — https://cdn.shopify.com/s/files/1/0620/4866/5821/files/sds_xm_waterless_wash.pdf?v=1714684462
4. MDSC catalog for name / SKU / image / pack sizes only — <https://marinedetailssupply.com/products/copy-of-boat-owner-economy-kit>
5. Mapping note — Mold system protocol also from manufacturer quick guide 104290QG.
6. Omissions — pH not extractable from published SDS text (scanned SDS); VOC not extractable from published SDS text; Relative density / flash point not extractable from published SDS text